



50 x 50mm, $\lambda/4$ Retarder Film (WP140HE)



Retarder Film with protective film removed



Stock **#14-723** 3-4 DAYS

⊖ 1 ⊕

€18,00

ADD TO CART

Qty 1-10
€18,00
Qty 11+
€15,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
588

Substrate: [Polymer Film WP140HE](#)

Length (mm): 50.00
Operating Temperature (°C): -40 to +120
Retardance: λ/4
Dimensions (mm): 50.0 x 50.0
Thickness (mm): 0.06 ±0.003
Transmission (%): >89
Type: Retarder Film
Dimensional Tolerance (mm): +0.0/-0.5
Construction: Polarizing Film
Phase Shift (°): 90.00
Haze (%): <1
Note: Fast axis is indicated by a black stripe on the protective film. This film should be removed before use.
Wavelength Range (nm): 400 - 700
Heat Resistance (°C x Hours): 80 x 1000
Width (mm): 50.00
Index of Refraction n_d: 1.58
Retardation (nm): 147 ±4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant