

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

50 X 50mm 470nm, Strobed, LED Backlight

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity LED Backlights

Stock **#83-288** [CONTACT US](#)



1



€843,00

ADD TO CART

Qty 1+

€843,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Blue

Model Number:
BL0202-470I3

Operating Temperature (°C):
0 to 65

Dimensions (mm): 72 H x 72 W x 12 D
Wavelength (nm): 470.00
LED Lifetime (hours): 50,000
Wavelength Tolerance (nm): ±25
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of LEDs: 48.00
Number of Channels: 1.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Uniformity (%): ±6 over Illuminated Area (Dependent on Working Distance)
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Strobed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)