

[All Products](#) / [Optics](#) / [Polarization](#)
/ [Circular Polarizers \(CP42HE and](#)

[See all 23 Products in Family](#)

50 x 50mm Left

CP42HE)



1

€30⁰⁰

Submit

Select Your Country/Region: European Union

Submit



ADD TO CART

Volume Pricing	
Qty 1-5	€30,00 each
Qty 6-25	€24,50 each
Need More?	Request Quote

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	Spec Sheets:pdf
eDrawing:eprt	
EO Spec Sheet	Download All

Prices shown are exclusive of VAT/local taxes

General

Type: Left-Handed Circular Polarizer

Note: Polarization axis is parallel to marking on protective film.

Physical & Mechanical Properties

Length (mm): 50.00

Dimensions (mm): 50.0 x 50.0 +0.0/-0.5

Thickness (mm): 0.27 ±0.04

Construction: Circular Polarizing Film

Width (mm): 50.00

Optical Properties

Substrate: [Polymer Film CP42HE](#)

Transmission (%): 42

Wavelength Range (nm): 400 - 700

Polarization Efficiency (%): >99.90

Environmental & Durability Factors

Operating Temperature (°C): -40 to +80

Heat Resistance (°C x Hours): 80 x 500

Regulatory Compliance

RoHS 2015: [Compliant](#)

Certificate of Conformance: [View](#)

REACH 241: [Compliant](#)

Product Details

- Greater than 42% Transmission
- Available with Film or Plastic Substrate
- Right-Handed or Left-Handed Designs Available

Circular Polarizers (CP42HE and CP42HER) are ideal for reducing glare in a variety of imaging applications or for increasing the visibility of displays in bright environments. These circular polarizers feature excellent transmission of visible light from 400 – 700nm. The plastic substrate offers increased durability, while the film substrate offers increased flexibility and can be cut to fit an application's needs. Circular Polarizer performance will be achieved at 560nm and polarization directions available. The best length.

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular polarizer, visit our [Polarizing Tool](#). We'll provide an immediate quote, and can list. For fully customized polymer polarizers to

600mm, please visit our [Polarizing Film](#) manufacturing tolerances and restrictions are

Related Products



Compact Direct Mounts



Rotation Kinematic Mounts

Frequently Purchased Together



#49-578 - 1200 Grooves, 12.7mm Sq, 36.9° Groove Angle Grating

€115,00

Qty



#55-044 - HandPlunger (3cc Barrel), Dispenser Units

€37,25


Qty



#55-064 - 22 Gauge (50 Count), UV Blocking Tapered Tips

€61,50

Qty



#58-784 - 2" x 2" (20 lp/mm), Ronchi Ruling

€340,00

Qty



Resources

Media Type

- Application Note
- Technical Tool
- Video
- FAQ
- Glossary

APPLICATION NOTE

Introduction to Polarization

TECHNICAL TOOL

Laser-Cut Polymer Polarizer and Retarder...

APPLICATION NOTE

Polymer Polarizers and Retarders

APPLICATION NOTE

Polarizer Selection Guide

APPLICATION NOTE

Understanding Waveplates and Retarders

VIDEO

How Do 3D Movies Work? Polarization

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: