

50 x 50mm UV Fused Silica Ground Glass Optical Diffuser



Stock **#49-159** [CONTACT US](#)

- 1 + **€99,50**

ADD TO CART

Qty 1-10
€99,50
Qty 11+
€79,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
50.00 x 50.00

Grit: ☐
220

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 200 - 2200
Width (mm): 50.00
Length (mm): 50.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View