


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



OD 2.0 Shortpass Filters

Stock #15-235 3-4 DAYS



1



€45,00

ADD TO CART

Qty 1-9

€45,00

Qty 10+

€40,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):

6.00 x 6.00 +0.00/-0.20

Angle of Incidence (°):

0

Optical Density OD (Average):

≥2.0

Cut-Off Wavelength (nm): 500.00 ±10
Substrate: 
Length (mm): 6.00
Coating: Hard Coated
Rejection Wavelength (nm): 520 - 610
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 325 - 480
Type: Shortpass Filter
Width (mm): 6.00
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 325 - 610

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View