

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50.0/50.8mm Optic Dia., Kinematic Mount, 2-Screws



50/50.8mm Diameter Kinematic Mount, 2-Screws , #58-852

Stock #58-852 3-4 DAYS



1



€125,00

ADD TO CART

Qty 1-4

€125,00

Qty 5+

€112,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:  
Adjustable - Tip-Tilt

Type of Optics:  
Circular

Size of Compatible Optics (mm):  
50.0 - 50.8

|                                                                                            |
|--------------------------------------------------------------------------------------------|
| <b>Number of Adjustment Screws:</b><br>2                                                   |
| <b>Clear Aperture CA (mm):</b><br>45.9                                                     |
| <b>Travel (mm):</b><br>No Z-Axis Translation                                               |
| <b>Construction:</b><br>Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings |
| <b>Angle Tolerance (°):</b><br>0.2 per 0.25mm turn                                         |
| <b>Fine Tilt Angle (°):</b><br>±5                                                          |
| <b>Fine Tip Angle (°):</b><br>±5                                                           |
| <b>Sensitivity per 1° Knob Rotation (arcsec):</b><br>2.3                                   |
| <b>Thermal Stability (μrad):</b><br><5                                                     |
| <b>Adjustment Screw Pitch (mm):</b><br>0.25                                                |
| <b>Compatible Post:</b><br>M4 x0.7, 8-32                                                   |
| <b>Min. Thickness of Compatible Optics (mm):</b><br>2.0                                    |
| <b>Pointing Stability (μrad):</b><br>1.3                                                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |