

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

50.8 X 50.8mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #69-250 ☐ In Stock



1



€32,50

ADD TO CART

Qty 1-5

€32,50

Qty 6+

€26,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm): 50.8 x50.8 ±0.76
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 50.80
Width (mm): 50.80

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant