

# 50.8mm Clear Aperture 33R/67T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock **#39-484** [CONTACT US](#)

-

1

+

**€291,00**

ADD TO CART

Qty 1-10

€291,00

Qty 11+

€247,40

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Clear Aperture CA (mm):**  
50.8

**Coating:**  
Dielectric

**Coating Specification:**

|                                                               |
|---------------------------------------------------------------|
| 33/67 @ 400 - 700nm                                           |
| <b>Construction:</b><br>Pellicle                              |
| <b>Diameter (mm):</b><br>63.50                                |
| <b>Housing:</b><br>Black Anodized Aluminum                    |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.5           |
| <b>Mount Thickness (mm):</b><br>6.35                          |
| <b>Reflection/Transmission Ratio (R/T):</b><br>33/67 $\pm$ 5% |
| <b>Substrate:</b> <input type="checkbox"/><br>Nitrocellulose  |
| <b>Surface Quality:</b><br>40-20                              |
| <b>Type:</b><br>Pellicle Beamsplitter                         |
| <b>Wavelength Range (nm):</b><br>400 - 700                    |
| <b>Mounting Threads:</b><br>2-56                              |
| <b>Thickness (<math>\mu</math>m):</b><br>2 +0.3/-0.0          |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>REACH 201:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |