

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

50.8mm Dia, 650 - 1100nm, $\lambda/4$ Achromatic waveplate



Achromatic Waveplates (Retarders)

Stock #39-046 [CONTACT US](#)

- 1 + **€3.120,00**

ADD TO CART

Qty 1-5

€3.120,00

Qty 6+

€2.705,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
>34.0

Coating:
R_{avg} <0.75% @650 - 1100nm

Diameter (mm):
50.80

Substrate: Crystal Quartz and MgF₂
Retardance: λ/4
Surface Quality: 40-20
Thickness (mm): 6.00 ±0.2
Type: Achromatic Waveplate
Dimensional Tolerance (mm): +0/-0.25
Construction: Crystalline
Transmitted Wavefront, P-V: <λ/4 @ 632nm
Parallelism (arcsec): <10
Housing Tolerance (mm): +0/-0.25
Retardance Tolerance: λ/100 @ 20°C
Coating Specification: R_{avg} <0.75% @ 650 - 1100nm
Wavelength Range (nm): 650 - 1100
Damage Threshold, By Design: >5 J/cm² @ 1064nm, 10ns, 10Hz
Configuration: Air Spaced

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant