

TECHSPEC® 50.8mm Dia., Uncoated, IR Ultrafast Thin Window



Stock **#11-754** ☐ In Stock

- 1 + **€215,00**

ADD TO CART

Qty 1-5
€215,00

Qty 6+
€193,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Uncoated

Diameter (mm):
50.80 +0.00/-0.10

Substrate: ☐
[Fused Silica](#) IR Grade

Index of Refraction n_d: 1.458
Surface Quality: 20-10
Thickness (mm): 1.00 ±0.10
Type: Ultrafast Window
Bevel: Protective as needed
Clear Aperture (%): 90
Transmitted Wavefront, P-V: $\lambda/6$
Abbe Number (v_d): 67.8
Parallelism (arcsec): ≤30
Wavelength Range (nm): 200 - 3500
Fused Silica Grade: 7979 0G
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View