

## 50.8mm Diameter, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#69-249** **20+ In Stock**

€41.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€41,00 each
Qty 6-25	€33,00 each
Qty 26-99	€26,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Flat Mirror **Type:**

#### Physical & Mechanical Properties

50.80 ±0.76 **Diameter (mm):**

**Bevel:**

Protective as needed

>90 **Clear Aperture (%):**

3.00 Nominal **Thickness (mm):**

## Optical Properties

4 - 6λ **Surface Flatness (P-V):**

Float Glass **Substrate:** □

80-50 **Surface Quality:**

R<sub>avg</sub> >85% @400 - 700nm **Coating Specification:**

Protected Aluminum (400-700nm) **Coating:**

Metal **Coating Type:**

45.00 **Angle of Incidence (°):**

400 - 700 **Wavelength Range (nm):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**


## Product Details

- Wide Variety of Shapes and Sizes Available
- >85% Reflection of Visible Light
- [Contact Us](#) for Custom Sizes

4 - 6λ First Surface Mirrors are an economical choice for a wide range of applications. First surface mirrors feature high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in circular, square, and rectangular dimensions. Rectangular 4 - 6λ First Surface Mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. The mirrors have a protected aluminum coating, and they reflect greater than 85% of visible light.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



## Quote Your Size

## Compatible Mounts