

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50.8mm Dia. Linear Plastic Polarizer (XP42-200)



Stock #85-922 3-4 DAYS

-

1

+

 €37,00

ADD TO CART

Qty 1-5

€37,00

Qty 6+

€30,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.80 +0.0/-0.3

Extinction Ratio:
9000:1

Substrate: ☐
[XP42-200 on PMMA](#)

Operating Temperature (°C):

-40 to +80
Thickness (mm): 2.22 ±0.25
Transmission (%): Single: 42 Parallel: 36 Crossed: <0.004
Type: Linear Polarizer
Construction: Polarizing Film on PMMA
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
