

50.0/50.8mm Optic Dia., 5 Axes Optical Mount



Stock **#13-778** 1 In Stock

-

1

+

€840^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€840,00 each
Qty 5-9	€798,10 each
Qty 10+	€714,10 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Adjustable - Linear (XYZ) & Tip-Tilt

Type:

Circular	Type of Optics:
Physical & Mechanical Properties	
46.0	Clear Aperture CA (mm):
±2.0 in X and Y, ±1.5 in Z	Travel (mm):
0.66	Weight (kg):
Black Anodized Aluminum	Construction:
±2	Tip/Tilt Angle (°):
Threading & Mounting	
50.0 - 50.8	Size of Compatible Optics (mm):
12.5 (Max)	Thickness of Compatible Optics (mm):
M6 x 1.0	Compatible Post:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

PRODUCT DETAILS

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
 - Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
 - M6 Mounting Threads
- Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

TECHNICAL INFORMATION



