

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC UV Fused Silica Aspheric Lenses



Stock #17-337 3-4 DAYS

[Other Coating Options](#)



1



€845,00

ADD TO CART

Qty 1-5

€845,00

Qty 6+

€676,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0/-0.025

Effective Focal Length EFL (mm): 100.00 @ 355nm
Numerical Aperture NA: 0.23
Back Focal Length BFL (mm): 91.50
Substrate: Fused Silica (Coming 7980)
Aspheric Design Wavelength (nm): 355
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <1
Surface Quality: 40-20
Clear Aperture CA (mm): 45
Edge Thickness ET (mm): 5.73
Center Thickness CT (mm): 14.00 ±0.1
f#: 2
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Conjugate Distance: Infinite
Power (diopters): 10.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View