

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #15-099 [CONTACT US](#)



1



€2.436,00

ADD TO CART

Qty 1+

€2.436,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Optical Density OD (Average):
≥4.0

Full Width-Half Max FWHM (nm):
10.00

Filters Included :
Center Wavelengths: [266nm](#), [355nm](#), [532nm](#),
[1064nm](#)

Coating: Hard Coated
Type: Bandpass Filter
Typical Applications: Nd:YAG Laser Line Cleanup
Wavelength: Nd:YAG
Number of Filters: 4
Environmental Durability: Humidity: MIL-STD 810.F, Method 507.4
Physical Durability: Adhesion: MIL-C-48497A, 3.4.1.1 Abrasion: MIL-C-48497A, 3.4.1.3 Temperature: MIL-C-48497A, 3.4.2.1 Cleaning: MIL-C-48497A, 3.4.2.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View