

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

50mm Dia. x 100mm FL Protected Aluminum, Concave Mirror



Stock #43-471 ☐ In Stock



1



€55,00

ADD TO CART

Qty 1-49

€55,00

Qty 50+

€46,50

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐

[N-BK7](#)

Focal Length Tolerance (%):

±2

Surface Quality:

80-50

Diameter (mm):

|                                                                                                            |
|------------------------------------------------------------------------------------------------------------|
| 50.00 ±0.50                                                                                                |
| <b>Effective Focal Length EFL (mm):</b><br>100.00                                                          |
| <b>Radius of Curvature (mm):</b><br>200.00                                                                 |
| <b>Aperture (f/#):</b><br>f/2                                                                              |
| <b>Coating:</b><br>Protected Aluminum (400-2000nm)                                                         |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >85% @400 - 700nm<br>R <sub>avg</sub> >90% @400 - 2000nm |
| <b>Coating Type:</b><br>Metal                                                                              |
| <b>Clear Aperture (%):</b><br>90                                                                           |
| <b>Edge Thickness ET (mm):</b><br>6.0                                                                      |
| <b>Radius R<sub>1</sub> (mm):</b><br>200.00                                                                |
| <b>Thickness Tolerance (mm):</b><br>±0.5                                                                   |
| <b>Type:</b><br>Spherical Mirror                                                                           |
| <b>Wavelength Range (nm):</b><br>400 - 2000                                                                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |