

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50mm Dia. X 75mm FL, 3-5µm Coated Germanium Meniscus Lens



Stock #87-965 3-4 DAYS



1



€1.094,00

ADD TO CART

Qty 1-5

€1.094,00

Qty 6+

€875,20

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Effective Focal Length EFL (mm):
75.00

Substrate: ☐
Germanium (Ge)

f/#:

1.5
Numerical Aperture NA: 0.33
Coating: BBAR (3000-5000nm)
Type: Meniscus Lens
Wavelength Range (nm): 3000 - 5000
Back Focal Length BFL (mm): 71.56
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Coating Specification: R _{avg} <3.0% @ 3 - 5µm
Edge Thickness ET (mm): 3.5
Focal Length Specification Wavelength (µm): 10.6
Radius R₁ (mm): 81.89
Radius R₂ (mm): 122.77
Surface Quality: 60-40
Wavelength Range (µm): 3 - 5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant