

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50mm Dia X -200mm FL, Enhanced Aluminum, Convex Mirror



Convex Mirrors

Stock #87-675 [CONTACT US](#)

- 1 + €70,50

ADD TO CART

Qty 1-5
€70,50

Qty 6+
€56,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Focal Length FL (mm):
-200.00

Center Thickness CT (mm):
5.00

Clear Aperture (%) : 90.00
Coating : Enhanced Aluminum (450-650nm)
Coating Specification : R _{avg} >95% @ 450 - 650nm
Coating Type : Metal
Dimensional Tolerance (mm) : +0.0/-0.1
Edge Thickness ET (mm) : 4.21
Focal Length Tolerance (%) : ±2
Radius R (mm) : 400.0
Substrate : ☐ N-BK7
Surface Accuracy : λ/2
Surface Quality : 60-40
Thickness Tolerance (mm) : ±0.1
Type : Spherical Mirror
Wavelength Range (nm) : 450 - 650

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant