

50mm Dia x -25.8mm FL Enhanced Aluminum Coated, Convex Mirror



Stock **#64-065** 3-4 DAYS

- 1 + **€56,00**

ADD TO CART

Qty 1-5
€56,00

Qty 6+
€50,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.00/-0.10

Focal Length FL (mm):
-25.80

Center Thickness CT (mm):
10.00

Clear Aperture (%):

Coating:
Enhanced Aluminum (450-650nm)

Coating Specification:
R_{avg} >95% @ 450 - 650nm

Coating Type:
Metal

Edge Thickness ET (mm):
3.55

Focal Length Tolerance (%):
±2

Radius R (mm):
51.68

Substrate: ☐
[N-BK7](#)

Surface Quality:
60-40

Type:
Spherical Mirror

Wavelength Range (nm):
450 - 650

Damage Threshold, Reference: ☐
0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
