

TECHSPEC® 50mm Dia x -25mm FL, Protected Gold, Convex Mirror



Convex Mirrors

Stock **#87-694** 3-4 DAYS

⊖ 1 ⊕ **€89,50**

ADD TO CART

Qty 1-5
€89,50

Qty 6+
€71,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Focal Length FL (mm):
-25.00

Center Thickness CT (mm):
8.00

Clear Aperture (%): 90.00
Coating: Protected Gold (700-10000nm)
Coating Specification: R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 1.30
Focal Length Tolerance (%): ±2
Radius R (mm): 50.0
Substrate: ☐ N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 700 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant