

50mm Diameter, 45° AOI, Hot Mirror



Hot Mirrors

Stock #55-233 ☐ In Stock

-

1

+

 €60,00

ADD TO CART

Qty 1-9
€60,00

Qty 10+
€52,80

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
45.00

Coating:
Hot Mirror, 45°

Diameter (mm):
50.00 ±0.25

Substrate:  BOROFLOAT®
Reflection (%) : >90, 750 - 1125nm
Surface Quality : 80-50
Thickness (mm) : 3.30
Transmission (%) : >85, 425 - 675nm
Type : Dichroic Filter
Coating Specification : Surface 1: 45° Hot Mirror Surface 2: None
Wavelength Range (nm) : 425 - 1125
Surface Flatness (P-V) : 4 - 6λ
Coating Type : Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant