

TECHSPEC® 50mm Diameter 50R/50T, VIS λ/10 Plate Beamsplitter



TECHSPEC® λ/10 Plate Beamsplitters

Stock **#34-416** ☒ In Stock

⊖

1

⊕

€272,00

ADD TO CART

Qty 1-5

€272,00

Qty 6+

€217,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating Specification:

Surface 1: 50/50 ±5% @ 550nm, ±10% @ 400 - 700nm
Surface 2: AR R_{avg} ≤1%, R_{abs} ≤2% @ 400 - 700nm

Construction:

Plate

Diameter (mm): 50.00
Dimensional Tolerance (mm): ±0.10
Edges: Protective Bevel as needed
Reflection/Transmission Ratio (R/T): 50/50
Substrate: Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.20
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700
Wedge Angle: 30 arcmin

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant