

50mm Diameter 600 Grit Ground Glass Diffuser



Stock #38-788 **11 In Stock**

€20⁷⁵

ADD TO CART

Volume Pricing	
Qty 1-10	€20,75 each
Qty 11+	€18,75 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Ground Glass Diffuser **Type:**
Sandblasted on first surface **Note:**

Physical & Mechanical Properties

50.00 ±0.25 **Diameter (mm):**

Ground **Edges:**

600 **Grit:**

1.60 **Thickness (mm):**

Optical Properties

Uncoated **Coating:**

Float Glass **Substrate:**

350 - 2000 **Wavelength Range (nm):**

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)


Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



Quote Your Size

Compatible Mounts