

TECHSPEC® 50mm, Enhanced Aluminum Coated, N-BK7 90° Specialty Mirror



Stock **#47-006** 3-4 DAYS

⊖ 1 ⊕ **€360,00**

ADD TO CART

Qty 1-5
€360,00
Qty 6+
€288,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
49.4

Coating:
Enhanced Aluminum (450-650nm)

Substrate: ☐
N-BK7

Surface Quality: 40-20
Type: Right Angle Mirror
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture (%): 90.00
Length of Hypotenuse (mm): 70.70
Length of Legs (mm): 50.00
Coating Specification: R_{avg} >95% @ 450 - 650nm
Wavelength Range (nm): 450 - 650
Surface Flatness (P-V): λ/4
Coating Type: Metal
Damage Threshold, Reference:  0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant