

50mm Focal Length Lens, 1" Sensor Format



1" Format Fixed Focal Length Lenses



Stock **#63-248** **8 In Stock**

[Similar Products](#)

-

1

+

 €715⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€715,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

1" Format Fixed Focal Length Lenses

Series:

Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:
49.00	Length (mm):
47.5	Maximum Diameter (mm):
47.5	Outer Diameter (mm):
200	Weight (g):
Optical Properties	
14.5°	Horizontal Field of View, 1" Sensor:
16.00	Maximum Image Circle (mm):
<0.05	TV Distortion (%):
50.00	Focal Length FL (mm):
500 - ∞	Working Distance (mm):
f/1.4 - f/16	Aperture (f/#):
< 0.05%	Maximum Distortion (%):
VS	Lens Wavelength Range:
Sensor	
1"	Maximum Sensor Format:
5.00	Pixel Size (µm):
Threading & Mounting	
M40.5 x 0.50	Filter Thread:
C-Mbunt	Mount:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

PRODUCT DETAILS

- Up to 1", C-Mount Lens
- "Fast" Lenses for Increased Throughput
- 4.7mm to 75mm Focal Length

1" Format Fixed Focal Length Lenses provide high throughput and high resolution across the entire camera sensor, allowing for excellent imaging even in less-than-ideal lighting conditions. Offered in 9 focal lengths from 4.7mm to 75mm, this complete family covers many of the applications in the market today. Engineered to minimize distortion, these lenses provide a perfect image for a human operator or an automated system. 1" Format Fixed Focal Length Lenses also feature a standard C-Mbunt lens mount for easy integration with the most common machine vision [cameras](#) we offer. All lenses feature front filter threading to attach to your choice of [optical filter](#).