

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50mm N-BK7 wedged window

See More by SCHOTT Optical Components



Stock #34-246 3-4 DAYS



1



€177,50

ADD TO CART

Qty 1-5

€177,50

Qty 6+

€142,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
45.00

Diameter (mm):
50.00 +0.0/-0.10

Thickness (mm):
3.00 ±0.20

Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Edges: Fine Ground
Index of Refraction n_d: 1.516
Substrate:  N-BK7
Surface Flatness (P-V): λ/10 over 25mm Aperture
Surface Quality: 20-10
Type: Wedged Window
Wavelength Range (nm): 350 - 2200
Young's Modulus (GPa): 82
Wedge Angle: 30' ±10'

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant