

50mW, 532nm LC Turnkey Laser Fiber SMA



Low Cost Turnkey Laser & Power Supply (Included)



Stock #19-486 3-4 DAYS



1



€3.325,00

ADD TO CART

Qty 1-9

€3.325,00

Qty 10+

€2.993,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Output Power (mW):
50

Power Stability (%):
<2% RMS over 4 hours

Dimensions (mm): 142.5 x 60 x 50
Wavelength (nm): 532.00
Wavelength Tolerance (nm): ±2
Power Supply: 88 x 145 x 83
Warm-Up Time (minutes): <10
Power Requirement: 90-264VAC
Modulation Frequency (kHz): 1
Output Type: Fiber Coupled
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Green
Connector: SMA
Beam Height from Base Plate (mm): 27.4
Mean Time to Failure MTTF (hours): 10000
Fiber Numerical Aperture NA (1/e²): 0.22

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
