

50X Mitutoyo Plan UV Infinity Corrected Objective

See More by [Mitutoyo](#)



Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives

Stock **#56-321** [CONTACT US](#)

- 1 +

€17.955,00

ADD TO CART

Qty 1+

€17.955,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Design Wavelength DWL (nm):
266, 532

Horizontal Field of View, 1/2" Sensor:
0.13mm

Horizontal Field of View, 2/3" Sensor:
0.18mm

Focal Length FL (mm): 4.00
Model Number: 378-838-8
Length excluding Threads (mm): 83.00
Magnification: 50X
Maximum Diameter (mm): 34
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.40
Mounting Threads: M26 x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (μm): 0.7
Depth of Field (μm): 1.70
Field of View, 24 Diameter Field Eyepiece (mm): 0.48
Field of View, 18 Diameter Field Eyepiece (mm): 0.36
Operating Temperature (°C): -5 to +45
Operating Humidity: 20 - 80%
Working Distance (mm): 12.0
Weight (g): 400.00
Note: Example Application: passivation (insulation films) of semiconductor circuits and repair of color filters of LCD panels (defect repair)
Style: Infinity Corrected
Manufacturer: Mitutoyo
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View