

50x50mm Half Mirror Coaxial Light Blue

See More by [CCS](#)



Stock **#21-837** 1 In Stock

-

1

+

€2.720⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.720,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

LFV3-G-50BL

Model Number:

LED Illuminator

Type of Illumination:

CCS	Manufacturer:
Coaxial Light	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
W60 mm xD 84 mm xH 57 mm	Dimensions (mm):
285	Weight (g):
52 mm x52 mm	Active Area (mm):
Optical Properties	
Blue	Color:
470.00	Wavelength (nm):
Electrical	
15	Power Consumption (W):
Hardware & Interface Connectivity	
24	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #73-491 Europe: #73-491 Japan: #89-513 Korea: #33-773 China: #73-491	
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Unique Design Prevents Ghost Images
- Available in Red, White, and Blue
- Ideal for Use with High Resolution Cameras

CCS High-Resolution Coaxial Lights are designed to provide diffused lighting for high-resolution imaging of shiny, flat surfaces. Designed to prevent ghost reflections and achieve higher system resolution, these coaxial lights integrate a unique thin beamsplitter to minimize deviation through in the imaging path. CCS High-Resolution Coaxial Lights are ideal for industrial imaging applications including inspection of glossy surfaces, pattern detection on PCBs, and measuring dimensions of glass.

TECHNICAL INFORMATION

