

50x50mm Half Mirror Coaxial Light Red

See More by [CCS](#)



Stock **#21-835** 1 In Stock

-

1

+

€3.105⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€3.105,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
LFV3-G-50RD	Model Number:
LED Illuminator	Type of Illumination:
CCS	Manufacturer:
Coaxial Light	Geometry:

Constant	Illumination Mode:
Physical & Mechanical Properties	
W 60 mm x D 84 mm x H 57 mm	Dimensions (mm):
285	Weight (g):
52 mm x 52 mm	Active Area (mm):
Optical Properties	
Red	Color:
630	Wavelength (nm):
Electrical	
17	Power Consumption (W):
Hardware & Interface Connectivity	
24	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #73-491 Europe: #73-491 Japan: #89-513 Korea: #33-773 China: #73-491	
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Unique Design Prevents Ghost Images
- Available in Red, White, and Blue
- Ideal for Use with High Resolution Cameras

CCS High-Resolution Coaxial Lights are designed to provide diffused lighting for high-resolution imaging of shiny, flat surfaces. Designed to prevent ghost reflections and achieve higher system resolution, these coaxial lights integrate a unique thin beamsplitter to minimize deviation through in the imaging path. CCS High-Resolution Coaxial Lights are ideal for industrial imaging applications including inspection of glossy surfaces, pattern detection on PCBs, and measuring dimensions of glass.

Technical Information

