

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Molded Diffuse Aspheric Condenser Lenses

Stock #22-686 3-4 DAYS



1



€55,00

ADD TO CART

Qty 1-10

€55,00

Qty 11+

€49,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
51.68 ±0.20

Effective Focal Length EFL (mm):
34.00

Numerical Aperture NA:
0.70

Back Focal Length BFL (mm): 18.10
Substrate:  Tritan
Focal Length Tolerance (%): ±7
Coating: Uncoated
Centering (arcmin): ≤25
Surface Quality: As Molded
Clear Aperture CA (mm): 43.20
Edge Thickness ET (mm): 3.20
Center Thickness CT (mm): 24.24 ±0.30
f/#: 0.71
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 48
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite
Note: Maximum of 5 imperfections allowed with an area of 0.8mm, per ISO 10110-7 specification of 5/5 x0.63. Click here for more information on the ISO 10110 surface quality specification.
Grit: Smooth

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant