

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

52 X 120mm, Red, EuroBrite™ Ring Light

See More by [Advanced Illumination](#)



AI EuroBrite Ring Light



Stock #33-448 3-4 DAYS

- 1 + €312,00

ADD TO CART

Qty 1+

€312,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Operating Lifetime (hours):
50,000

Input Voltage (V): 24V nominal (min. 22 / max. 28)
Model Number: RL-S052120M-625
Operating Temperature (°C): 0 - 60
Dimensions (mm): 120 x 120 x 30
Wavelength (nm): 625.00
Weight (g): 173.00
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Type of Illumination: LED Illuminator
Note: See Technical Information Tab for Typical Intensity
Geometry: Ring Light
Maximum Input Current: 0.42 - 0.49A
Analog Intensity Control: 10% @ 0.7V, 100% @ 10V
Trigger-to-Pulse Latency: 10µm
Illumination Mode: Strobed or Constant
Environmental Rating: IP67

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)