

Coherent® StingRay™ Line Generator 1231493 | 520nm, 5mW, 30° Fan Angle

See More by [Coherent®](#)



Stock #86-851 3-4 DAYS

- 1 +

€1.060,00

ADD TO CART

Qty 1+
€1.060,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
-10 to +50

Output Power (mW):
5

Spatial Mode: TEM ₀₀
Wavelength (nm): 520.00
Mode Quality, M²: <1.5
Wavelength Tolerance (nm): ±10
Power Supply: Power Supply Required and Sold Separately. USA: #86-878 Europe: #86-878 Japan: #86-878 Korea: #86-878 China: #86-878
Storage Temperature (°C): -20 to +60
Pointing Stability (μrad/°C): <10
Modulation Frequency (kHz): Max Analog: 500
Electrical Leads/ Pin Connections: Hirose HR-10P-12S
Manufacturer: Coherent®
Output Type: Free Space
Type of Laser: Diode
Laser Class - CDRH: II
Color: Green
Fan Angle (°): 30.00
Input Voltage (V): 5 - 24 DC
Model Number: 1231493
Length (mm): 97.80

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View