

Coherent® StingRay™ Laser Diode Module 1253668 | 520nm, 10mW

See More by [Coherent®](#)



Stock #87-522 3-4 DAYS

- 1 +

€920,00

ADD TO CART

Qty 1+

€920,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
-10 to +50

Output Power (mW):
10

Spatial Mode: TEM ₀₀
Wavelength (nm): 520.00
Mode Quality, M²: <1.5
Wavelength Tolerance (nm): ±10
Power Supply: Power Supply Required and Sold Separately. USA: #86-878 Europe: #86-878 Japan: #86-878 Korea: #86-878 China: #86-878
Storage Temperature (°C): -20 to +60
Pointing Stability (μrad/°C): <10
Modulation Frequency (kHz): Max Analog: 500
Electrical Leads/ Pin Connections: Hirose HR-10P-12S
Manufacturer: Coherent®
Output Type: Free Space
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Green
Input Voltage (V): 5 - 24 DC
Model Number: 1253668
Length (mm): 95.10

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View