

# 532nm Flat Top Beam Shaper | πShaper 12\_12\_532\_HP

See More by [AdlOptica](#)



Stock **#15-496** [CONTACT US](#)

-

1

+

€8.801,00

ADD TO CART

|           |
|-----------|
| Qty 1-4   |
| €8.801,00 |

|           |
|-----------|
| Qty 5+    |
| €7.921,00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):  
532

Diameter (mm):  
42.00

Entrance Beam Diameter, 1/e<sup>2</sup> (mm):  
12.0 - 12.1

|                                                                                         |
|-----------------------------------------------------------------------------------------|
| <b>Model Number:</b><br>πShaper 12_12_532_HP                                            |
| <b>Length (mm):</b><br>358.00                                                           |
| <b>Mounting Threads:</b><br>M27 x 1                                                     |
| <b>Type:</b><br>Beam Shaper                                                             |
| <b>Weight (g):</b><br><530                                                              |
| <b>Wavelength Range (nm):</b><br>515 - 550                                              |
| <b>Style:</b><br>Flat Top                                                               |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>3 J/cm² @ 5ns (typical) |
| <b>Output Diameter, FWHM (mm):</b><br>11.8                                              |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |