

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 5mm Diameter, 1064nm V-Coat, λ/4 N-BK7 Window

See More by [SCHOTT Optical Components](#)



Stock #49-145 3-4 DAYS



1



€79,00

ADD TO CART

Qty 1-5

€79,00

Qty 6+

€63,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture CA (mm):
4.50

Coating:
Laser V-Coat (1064nm)

Coating Specification: R_{abs} <0.25% @ 1064nm
Diameter (mm): 5.00 +0.00/-0.25
Thickness (mm): 2.00 ±0.20
Design Wavelength DWL (nm): 1064
Parallelism (arcmin): ≤1
Substrate: N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 60-40
Type: Laser Line Window
Young's Modulus (GPa): 82
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Index of Refraction n_d: 1.516
Poisson's Ratio: 0.206
Abbe Number (v_d): 64.17
Edges: Fine Ground

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant