

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

5mm Diameter, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #27-400 3-4 DAYS



1



€12,00

ADD TO CART

Qty 1-5

€12,00

Qty 6+

€10,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
5.00 ±0.76

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality: 80-50
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Thickness (mm): 1.00 Nominal
Thickness Tolerance (mm): Nominal
Type: Flat Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
