

TECHSPEC® 5mm H x 10mm L x 20mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#43-857** ☐ In Stock

-

1

+

€109,00

ADD TO CART

Qty 1-5
€109,00
Qty 6+
€87,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm): 20.00
Substrate: ☐ N-BK7
f/#: 4

Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 19.34
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 5.0 x 10.0
Edge Thickness ET (mm): 0.69
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 10.32
Surface Quality: 60-40
Tilt Tolerance (mm): ±0.1 over H
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View