

## 5mm MegaPixel Fixed Focal Length Lens



MegaPixel Fixed Focal Length Lenses

Stock **#64-867** **1 In Stock**

€394<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€394,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Product Family:**  
MegaPixel Fixed Focal Length Lenses

**Type:**  
Fixed Focal Length Lens

### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**

45.50

Maximum Diameter (mm):

44.50

Outer Diameter (mm):

44.5

Weight (g):

102.00

Maximum Rear Protrusion (mm):

3.00

### Optical Properties

Field of View @ Min Working Distance (mm):

150.00

Horizontal Field of View, 1/2" Sensor:

65.50°

Maximum Image Circle (mm):

8.00

Focal Length FL (mm):

5.00

Working Distance (mm):

100 - 900

Aperture (f/#):

f/1.4 - f/16

Maximum Distortion (%):

-0.48

Lens Wavelength Range:

VIS

### Sensor

Maximum Sensor Format:

1/2"

Pixel Size (µm):

6.20

### Threading & Mounting

Filter Thread:

M43.0 x 0.75

Mount:

C-Mount

### Regulatory Compliance

RoHS 2015:

Exempt

Reach 224:

Contains SVHC(s)

Certificate of Conformance:

View

## Product Details

- Up to 2/3", C-Mount Lens
- Ideal for Machine Vision at an Economical Price
- 5mm to 75mm Focal Length

MegaPixel Fixed Focal Length Lenses are designed for high-resolution imaging. The lenses are ideal for machine vision applications with demanding space constraints. These lenses complement the resolution of many MegaPixel cameras with 1/2" or 2/3" formats. Low distortion and high resolution enable these economically priced lenses to produce sharp, high-contrast images compared to standard CCTV and compact lenses. MegaPixel Fixed Focal Length Lenses are available in focal lengths ranging from 5 to 75mm. Locking screws for the manual iris and focus allow these lenses to be used in high-vibration environments. Typical applications include [factory automation](#), inspection, and macro work.

**Note:** For #64-869 75mm FL Lens, remove focus limit screw to focus past 1.2m.

## Technical Information

### #64-867 5mm Megapixel Fixed Focal Length Lens



