

TECHSPEC® 5mm Uncoated Ultra Precision UV Fused Silica Right Angle Prism



Stock #35-900 3-4 DAYS

⊖ 1 ⊕ **€250,00**

ADD TO CART

Qty 1-5

€250,00

Qty 6+

€225,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
Uncoated

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Length of Hypotenuse (mm): 7.10
Length of Legs (mm): 5.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/20

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View