

5mW, 635nm Laser Bat Power ZAT, 60° X-Hair (Recertified 05-P)



Stock #19-540-RCD-05P **RECERTIFIED** 1 In Stock

- 1 + €298⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€298,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes



General

Crosshair **Style:**
 1M **Laser Class - CDRH:**

Physical & Mechanical Properties

162 **Weight (g):**
 124.00 **Length (mm):**

Optical Properties

635.00 **Wavelength (nm):**
 Red **Color:**
 60.00 **Fan Angle (°):**
 Up to 1,500mm **Focus Range (mm):**

Electrical

5 **Output Power (mW):**

Hardware & Interface Connectivity

1 AA Battery (Not Included) **Power Requirement:**
 Free Space **Output Type:**

Environmental & Durability Factors

IP40 **Environmental Rating:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Bright Red 635nm Wavelength
- Line, Crosshair, or Dot Projection
- Battery Powered Operation with a Fixed Focus
- Sturdy, Metal Housing

Z-Laser ZAT Battery Powered Lasers are ideal for positioning and alignment applications. Their battery powered design provides maneuverability by removing the need for a fixed power supply. IP40 rated, shock proof, and vibration proof with a sturdy, metal housing makes these lasers excellent for harsh environments and repeated use. Z-Laser ZAT Battery Powered Lasers are suitable for use in industrial environments such as Automotive, Paper, Wood, Ceramic, and Metal. Available with 1 or 5mW output powers, the lasers utilize one AA battery (not included) ensuring easy maintenance and an extended lifetime.