

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

5mW, 780nm Alignment Laser Diode



Red and IR Alignment Laser Diode

Stock #37-036 3-4 DAYS



1



€134,00

ADD TO CART

Qty 1-9

€134,00

Qty 10+

€117,90

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
-10 to 50

Operating Voltage (V):
5

Output Power (mW): 5
Wavelength (nm): 780.00
Wavelength Tolerance (nm): ±5
Power Supply: Power Supply Required and Sold Separately: USA: #83-855 Europe: #83-855 Japan: #13-640 Korea: #33-770 China: #83-855
Modulation Frequency (kHz): 0 - 10
Beam Diameter (mm): 3 x 1 Typical
Beam Divergence (mrad): Major Axis: 0.4 Minor Axis: 0.2
Laser Class - CDRH: IIIb
Color: Infrared
Length (mm): 36.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant