

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

5mW Random Polarization, Lasos HeNe Laser



Stock #35-209 ☐ In Stock

-

1

+

 €700,00

ADD TO CART

Qty 1+

€700,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Output Power (mW):
5

Polarization:
Random

Wavelength (nm):
632.80

Weight (g):
650.00

Laser Class - IEC:
3B

Power Supply:
Power Supply Required and Sold Separately.
USA: [#35-219](#)
Europe: [#35-219](#)
Japan: Not Available
Korea: Not Available
China: Not Available

Static Alignment:
Centered to Outer Cylinder: ≤0.5mm
Parallel to Outer Cylinder: ≤1.25

Pointing Stability (mrad/°C):
≤0.1

RMS Noise:
30Hz–10MHz ≤1%

Beam Diameter (mm):
0.8

Type of Laser:
HeNe

Beam Divergence (mrad):
≤1.1

Laser Class - CDRH:
IIIb

Length (mm):
388.00

Longitudinal Mode Spacing, Nominal (MHz):
438.00

Diameter of Laser Head (mm):
45

Length of Laser Head (mm):
388

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)