

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

5X 65mm W.D, In-Line Illumination Telecentric Lens



Stock #62-794 3-4 DAYS



1



€1.190,00

ADD TO CART

Qty 1+

€1.190,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
92.00

Ferrule Diameter (inches):
0.312

Horizontal Field of View, 1/2" Sensor:
1.2mm

Horizontal Field of View, 2/3" Sensor:
1.8mm

Maximum Diameter (mm):
17.0

Horizontal Field of View @ Max Sensor Format: 1.8mm
Type: Telecentric Lens
Primary Magnification PMAG: 5X
Maximum Sensor Format: 2/3"
Working Distance (mm): 65.00
Mount: C-Mount
Style: In-Line Illumination
Aperture (f#): f/30.6
Distortion (%): ≤0.1
Compatible Light Guide/Source: 1/4" (0.312")
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View