

## 6 Watt, 230V, 365nm UV Curing Lamp



6 Watt, 230V, 365nm UV Curing Lamp, #86-805

Stock **#86-805** CLEARANCE **3 In Stock**

1  €350<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€350,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Note:**  
Voltage converter required for use in U.S.

### Optical Properties

**Wavelength (nm):**  
365.00

**Irradiance at 76.2mm (μW/cm<sup>2</sup>):**  
2300

### Hardware & Interface Connectivity

---

6W, 230V

**Power Requirement:**

---

## Regulatory Compliance

[View](#)

**Certificate of Conformance:**

---

## Product Details

Stands are not included, but recommended for hands free curing or analysis.

- 4-Watt and 6-Watt Models Centered at 365nm
- Stands are Available for Hands Free Curing
- Portable, High Intensity Design

Handheld UV Curing Lamps are portable benchtop lamps designed for a variety of applications including the fluorescence of stained gels, sterilization, or UV curing. These lamps feature ergonomically designed handles with conveniently placed on/off switches. These lamps are portable, with a high-intensity design. Handheld UV Curing Lamps are ideal for quickly curing Edmund Optics' full line of [Norland Optical Adhesives](#). These lamps are available in 4-watt and 6-watt models centered at 365nm.

**Note:** Stands are not included, but are recommended for hands free curing or analysis.

---