

[See all 23 Products in Family](#)

6", Blue 470nm, UltraSeal Washdown Bar Light

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Bar Lights

Stock **#18-625** CLEARANCE **1 In Stock**

⊖ 1 ⊕ €850^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€850,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

AL247M06-470IC **Model Number:**

50000 **LED Lifetime (hours):**

LED Illuminator **Type of Illumination:**

Note:
Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

Advanced Illumination	Manufacturer:
Bar Light	Geometry:
Constant	Illumination Mode:

Physical & Mechanical Properties

171.4 x 42.9 x 24	Dimensions (mm):
417	Weight (g):

Optical Properties

Blue	Color:
470	Wavelength (nm):

Electrical

0.35A	Minimum Input Current:
-------	-------------------------------

Hardware & Interface Connectivity

Flying Leads	Connector:
24V	Input Voltage (V):

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Environmental & Durability Factors

0 - 60	Operating Temperature (°C):
IP69K	Environmental Rating:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

Product Details

- IP69K Certified for Extreme Washdown Environments
 - Stainless Steel Housing
 - High Intensity Output up to 70,200 Lux
 - Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended
- Advanced Illumination UltraSeal Washdown Bar Lights offer intense, direct illumination up to 70,200 Lux while providing maximum protection in extreme environmental conditions. These IP69K certified Bar Lights were designed with a crevice-free design to withstand high temperature wash-down procedures and material buildup. The 316 stainless steel is FDA compliant, making them a suitable option for food or pharmaceutical inspection environments. Advanced Illumination UltraSeal Washdown Bar Lights are ideal for hygienic and aseptic manufacturing applications, such as prolonged liquid immersion and high-pressure steam cleaning common in food and beverage inspection and processing.
- Note:** Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.