

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 6" Diameter X 30" FL Protected Gold, Parabolic Mirror



Stock #32-070-566 [CONTACT US](#)



1



€856,00

ADD TO CART

Qty 1-4

€856,00

Qty 5+

€728,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate:

BOROFLOAT®

Focal Length Tolerance (%):

±1

Surface Quality:

60-40

Surface Accuracy:

N/8
Diameter (inches): 6.0 +0.06/-0
Diameter (mm): 152.40 +1.5/-0
Effective Focal Length EFL (inches): 30.0
Effective Focal Length EFL (mm): 762.00
Radius of Curvature (mm): 1,524.00
Aperture (f/#): f/5
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 138
Edge Thickness ET (inches): 1.00
Edge Thickness ET (mm): 25.40
Type: Parabolic Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: 0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant