

[See all 3 Products in Family](#)

## 6 Watt, 365nm Replacement Tube



#86-806

Stock **#86-806** CLEARANCE CONTACT US

- 1 + €34.<sup>50</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €34,50 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

### Regulatory Compliance

Certificate of Conformance:

[View](#)

### Product Details

- 4-Watt and 6-Watt Models Centered at 365nm
- Stands are Available for Hands Free Curing

- Portable, High Intensity Design

Handheld UV Curing Lamps are portable benchtop lamps designed for a variety of applications including the fluorescence of stained gels, sterilization, or UV curing. These lamps feature ergonomically designed handles with conveniently placed on/off switches. These lamps are portable, with a high-intensity design. Handheld UV Curing Lamps are ideal for quickly curing Edmund Optics' full line of [Norland Optical Adhesives](#). These lamps are available in 4-watt and 6-watt models centered at 365nm.

**Note:** Stands are not included, but are recommended for hands free curing or analysis.

---