

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

600 Grooves, 25mm Square, 1250nm Ruled Diffraction Grating



Reflective Ruled Diffraction Gratings

Stock #43-747 ■ In Stock



1



€134,00

ADD TO CART

Qty 1-10

€134,00

Qty 11+

€118,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):

600

Blaze Wavelength (nm):

1250

Blaze Angle (°):

22.02
Dimensions (mm): 25.0 x 25.0 ±0.5
Clear Aperture (%) : 90
Coating: Bare Aluminum
Construction: Ruled Grating
Direction of Grooves: Parallel to Short Dimension
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 25.00
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%) : 88
Peak Efficiency Avg, Typical (%) : >83

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View