See all 16 Products in Family

600 lp/mm, 1" x 3", Float Glass, Ronchi Ruling

Stock **#38-566** **3 In Stock**

- 1 + **€760**.00

ADD TO CART

Volume Pricing	
Qty 1-4	**€760,00** each
Qty 5+	**€722,80** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties

Length (inches):
3.00

Pattern Size (mm):
12.7 x 25.4

Thickness (mm):
1.10

Width (inches):
1.00

Optical Properties

Coating:
Vacuum Deposited Chrome

Frequency (lp/mm):
600.00

Substrate:
Float Glass

Optical Density OD (Average):
3.00

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 240:
Compliant

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and **Opal.**

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.

;